

START/STOP SERVICE S5

CONTINUOUS SERVICE S1

- Calculate acceleration torque on gearbox output :



F1 and **F2**: correction factors as per following chart.

GEARBOX RUNNING TIME DURING 1 FULL CYCLE											
	10 %	30 %	50 %	70 %	90 %						
F1	0,7	0,85	1	1,11	1,2						

NUMBER OF STARTS PER HOUR												
	1000 to 2000	2000 to 3000	3000 to 5000	5000 to 10000								
F2	1 to 1,35	1,35 to 1,45	1,45 to 1,6	1,6 to 1,9								

Intermediates values

To be interpolated



- Select the gearbox size in the column **Torque S5**:



Torque S5 > C2acc

- Calculate nominal torque on gearbox output



- Select the gearbox size in the column **Torque S1**:



Torque S1 > C2nom

LEGEND

C1acc (N.m): motor acceleration torque C1nom (N.m): nominal motor torque

C2acc (N.m): gearbox output acceleration torque C2nom (N.m): Gearbox output nominal torque

E-stop (N.m): gearbox output emergency torque (2 seconds duration maximum, applied a maximum of 25000 times over the gearbox life)

C1f (N.m): starting input friction torque (without any load on output)

N1: maximum input RPM to be achieved during a full cycle (S5 service) or input nominal RPM (S1 service)

i: exact gear ratio

Et (N.m/minute): Torsional stifness on output

ig (kg.m²): polar moment of inertia on input (to be added to coupling inertia, see page 10)

1 (%): gearbox efficiency at considered input RPM

Fr (N): permissible radial load on output shaft (applied at the middle of the shaft)

Fa (N): permissible axial load on output shaft

REVERSIBILITY CLASSES									
1	Total reversibility								
2	Uncertain reversibility								
3	Self-locking at N₁=0								


Notes: self-locking units can become reversible under vibrations. Indicated efficiency values are achieved after a 24 hours full load operation

TECHNICAL SPECIFICATIONS

N1		60	00		4000			3000)		2000			1000								
		Torque	r	Torque	Torque	r	Torque	Torque	r	Torque	Torque	r	Torque	Torque	r	E-stop	044	:	F4	Reversibility	r.	
	5.2:1	S5 11	89	\$1 8	\$5 13	88	\$1 9	\$5 15	87	\$1 11	\$5 18	86	\$1 14	\$5 23	84	46	0,03	ig 2.2 X 10-⁵	Et 2	class 1	Fr 1500	5
	7.25:1	11	88	8	14	87	9	15	86	11	18	85	14	24	82	46	0,03	1,51 X 10-6	2	1	1500	5
YNABOX	10.25:1	11	87	8	13	86	8	14	85	11	18	84	14	23	81	46	0,03	1,15 X 10-6	2	1	1500	
25	14.5:1	13	82	9	15	81	11	18	79	12	20	77	16	26	74	46	-	9,58 X 10 ⁻⁷	2	2	1500	
	19.5:1	13	80	9	15	78	11	18	76	12	20	74	16	26	70	46		8,67 X 10 ⁻⁷	2	2	1500	
	30:1 45:1	15 15	73 67	11	18 18	70 64	12 11	20 19	68 62	14	23	65 59	17 17	29 28	60 53	46 42	0,03	8 X 10 ⁻⁷ 7,77 X 10 ⁻⁷	2	3	1500 1500	
	60:1	14	62	10	16	59	11	19	56	13	21	53	15	25	48	35	0,03	7,6 X 10 ⁻⁷	2	3	1500	
	5.2:1	23	94	16	27	93	18	31	92	22	36	91	29	48	89	96	0,3	7,4 X 10-6	5	1	3800	
	7.25:1	23	92	17	28	91	19	32	90	23	37	89	30	48	86	96	0,3	5,6 X 10°	5	1	3800	
	10.25:1	24	90	17	29	89	20	34	88	23	39	87	30	51	81	96	0,3	5 X 10-6	5	1	3800	
YNABOX	14.5:1	27	87	19	31	85	22	35	83	26	41	81	33	52	77	96	0,3	4,4 X 10 ⁻⁶	5	2	3800	
35	19.5:1	28	84	20	32	82	22	35	80	26	42	78	33	50	73	96	0,2	4,2 X 10 ⁻⁶	5	2	3800	
	30:1 45:1	30	77 71	23	37 36	74 68	25 25	40	72 65	29 28	46 45	69 61	36 35	58 56	63 56	96 87	0,2	4 X 10 ⁻⁶ 3,9 X 10 ⁻⁶	5 5	3	3800	
	60:1	30	65	22	34	62	24	37	59	27	41	55	34	50	50	73	0,2	3,3 X 10 ⁻⁶	5	3	3800	
	90:1	28	57	21	32	53	23	35	50	26	39	46	32	46	41	72	0,1	2,31 X 10 ⁻⁶	5	3	3800	
	5.2:1	54	95	36	62	94	41	70	93	50	83	92	67	109	91	214	0,4	2,9 X 10⁵	9	1	5800	
	7.25:1	59	94	42	71	93	48	80	92	57	93	91	76	121	89	214	0,4	2,2 X 10 ⁻⁵	9	1	5800	
	10.25:1	68	93	46	80	92	53	88	91	62	98	90	80	128	88	214	0,4	1,5 X 10⁵	9	1	5800	
YNABOX	14.5:1	69	90	52	83	88	59	94	87	68	109	86	88	141	82	214	0,4	1,4 X 10 ⁻⁵	9	1	5800	
45	19.5:1 30:1	66 74	89	50 55	88	87 80	55 61	98 98	86 78	64 70	102 112	84 76	81 88	129 141	80 71	214 214	0,3	1 X 10 ⁻⁵	9	1 2	5800 5800	
	45:1	74	77	54	86	75	59	94	72	68	109	69	83	133	64	185	0,3	8,2 X 10 ⁻⁶	9	3	5800	
	60:1	69	73	50	78	70	55	86	68	62	97	64	75	116	59	170	0,2	7,3 X 10 ⁻⁶	9	3	5800	
	90:1	63	66	46	71	62	50	76	59	57	86	56	68	99	50	154	0,2	4,6 X 10 ⁻⁶	9	3	5800	
	5.2:1	85	95	60	103	94	68	116	94	82	137	93	111	181	91	307	0,6	7,5 X 10⁻⁵	20	1	7000	
	7.25:1	88	94	65	111	93	74	125	92	90	147	91	118	188	89	307	0,6	5,3 X 10 ⁻⁵	20	1	7000	
	10.25:1	102	92	76	132	90	87	145	89	103	165	88	133	206	85	307	0,6	4,5 X 10 ⁻⁵	20	1	7000	
YNABOX	14.5:1	96	90	71	115	88	82	133	87	96	155	85	123	190	82	307	0,6	3,8 X 10 ⁻⁵	20	1	7000	
55	19.5:1 30:1	101	88 82	77 83	123	87 80	94	139 148	85 78	101	162 169	83 75	128 136	205	80 70	307 307	0,4	3,1 X 10 ⁻⁵ 3,4 X 10 ⁻⁵	20	2	7000 7000	
	45:1	110	77	83	130	74	93	145	72	106	163	69	131	202	63	307	0,4	2,8 X 10 ⁻⁵	20	3	7000	
	60:1	110	73	82	128	69	91	141	67	103	158	63	126	194	58	286	0,3	2,6 X 10 ⁻⁵	20	3	7000	
	90:1	102	65	76	117	62	82	125	59	94	142	55	113	164	49	263	0,3	1,2 X 10 ⁻⁵	20	3	7000	
	5.2:1	128	95	90	153	95	105	179	94	126	210	93	169	275	91	497	0,8	1,6 X 10⁴	36	1	8800	
	7.25:1	123	95	91	155	94	103	174	93	125	206	92	165	264	90	497	0,8	9 X 10-5	36	1	8800	
	10.25:1	134	94	103	169	93	118	194	92	141	231	91	181	290	89	497	0,8	8 X 10 ⁻⁵	36	1	8800	H
MADOX	14.5:1 19.5:1	146 155	91	110	179 190	90	128 135	207	89 87	149 156	240 250	87 85	191 199	293 318	84 82	497 497	0,8	6,9 X 10 ⁻⁵ 5,5 X 10 ⁻⁵	36 36	1	8800	H
63	30:1	179	84	138	218	82	155	245	80	179	281	78	223	335	73	497	0,5	5,9 X 10 ⁻⁵	36	2	8800	
	45:1	163	80	123	193	77	137	214	75	156	239	72	193	287	67	403	0,5	5 X 10-⁵	36	3	8800	
	60:1	162	76	121	189	73		205	71	151	233	67	186	288	62	404	0,4	4,7 X 10 ⁻⁵	36	3	8800	1
	90:1	149	68	110	169	65	121	184	63	137	207	59	166	241	53	368	0,4	3,2 X 10 ⁻⁵	36	3	8800	1
	5.2:1	213	96	147	252	95	174	296	94	209	349	94	282	459	92	834	1	3,7 X 10⁴	50	1	10500	1
	7.25:1		95	139	236	94	161	270	93	196	321	92	256	409	90	834	1	2,5 X 10⁴	50	1	10500	
YNABOX	10.25:1		94	146 170	234 276	93		269 315	92 88	204 234	326 376	91	261 298	418 460	88	834	1	2,2 X 10 ⁻⁴ 1,9 X 10 ⁻⁴	50 50	1	10500 10500	
	19.5:1		89		270	88	195		87	234	362	87 85	288	434	84 81	834 834	0,6	1,9 X 10 ⁻⁴	50	2	10500	
75	30:1	252	86	186	294	84	212	334	82	248	386	80	309	460	75	834	0,6	1,6 X 10⁴	50	2	10500	•
	45:1	243	79	190	299	76		331	74	244	383	71	301	472	65	718	0,6	1,4 X 10 ⁻⁴	50	3	10500	
	60:1 90:1	225 218	75 68		272 257	72 64		300 280	69 62	221	334 316	66 57	272 255	395 370	60 52	657 625	0,5	1,3 X 10⁴ 8 X 10⁵	50 50	3	10500 10500	
																	5,5			Ü		
		332	96		387	95		460	95	327	546	94	445	725	92	1543	1,5	8,5 X 10 ⁻⁴	75	1	15800	
	7.25:1 10.25:1		95	263273	460	95		490	95 93	373	597	94	490 488	784	92	1543	1,5	6 X 10⁴	75 75	1	15800 15800	
	14.5:1		95 92	272	478 444	94	314 314	528 504	90	383	627 612	92 88	486	781 748	90 85	1543 1543	1,5 1,5	3,8 X 10 ⁻⁴ 3,2 X 10 ⁻⁴	75	1	15800	
THE STATE OF THE S	19.5:1		91	318	506	90	367	584	88	431	685	87	544	865	84	1543	0,8	2,5 X 10 ⁻⁴	75	1	15800	
	30:1	433	86	316	500	84	362	572	82	424	661	80	531	792	75	1543	0,8	2,6 X 10⁴	75	2	15800	1
	45:1	454	83	343	538	80	385	599	79	441	674	76	546	811	71	1255	0,8	1,9 X 10⁴	75	3	15800	
	60:1 90:1	432 394	80 74	328 298	512 459	77 70	364 332	559 505	75 68	412 372	622 562	72 64	507 460	761 667	67 59	1230 1114	0,5	1,7 X 10⁴ 1 X 10⁴	75 75	3	15800 15800	
			_		_	=																
	5.2:1	567	96	390	666	95		779	95	561	937	94	760	1239	92	2289	2	1,85 X 10 ⁻³	120	1	21500	
	7.25:1 10.25:1		95 95	417	680	95		795	95 93	599	976	94	802	1307	92	2289	2	1,3 X 10 ⁻³ 8,5 X 10 ⁻⁴	120	1	21500	
	10.25:1	630	95 93	449 450	786 720	94 92		878 830	93	638 630	1047 1014	92 90	827 810	1323 1247	90 87	2289 2289	2	8,5 X 10 ⁻⁴ 6,3 X 10 ⁻⁴	120 120	1	21500 21500	
IIIAD OX	19.5:1	670	92	510	815	91	589	943	90	705	1121	88	893	1349	85	2289	1	4,6 X 10 ⁻⁴	120	1	21500	
	30:1	790	88	597	955	87		1100	85	812	1299	83	1015	1512	79	2289	1	3,5 X 10⁴	120	2	21500	
	4= 4	776	85	583	915	82	665	1037	80	765	1168	78	947	1411	73	2152	1	3,3 X 10⁴	120	3	21500	1
	45:1 60:1	683	81	522	815	79	588	905	77	669	1030	73	826	1239	68	2094	0,8	3 X 10⁴	120	3	21500	

HOW TO ORDER

Use following codification to order your **DYNABOX**.



SERVO GEARSETS DYNASET WITH ADJUSTABLE BACKLASH

When **DYNABOX** servo gearheads cannot be used, the **DYNASET** servo gearsets, to be mounted in customed housing, are an interesting alternative.

Their performance are comparable to complete reducers, assuming following recommendations:

MOUNTING

Wormshaft: housing and bearing design should allow an axial shifting, necessary for backlash adjustment. The total adjustment range is obtained with a permissible displacement equal to W, as per page 18.

It is recommended, whenever possible, to use our backlash adjustment device, which is delivered preset (see page 19).

The front ball bearing (see page 19) must be engaged on the shaft after the complete gear assembly, and before the backlash adjustment operation.

Wheel ring: Arrows shown on wormshaft and wheel ring must be lined up during assembly (see page 18). As the bore \emptyset A tolerance is H6, it is recommended to grind the shaft with a tolerance k5. This will eliminate any runnout between the wheel ring and the shaft. In order to facilitate the connection between the 2 parts, heat the wheel ring up to 50°C.


After cooling, check that the wheel ring is no buckled, by applying a dial indicator on its face, while rotating the shaft.

Then, finish the pins bores ((xY) \emptyset S, see page 18) of the 2 assembled parts, as they are delivered pre-bored only. Otherwise, screws can be also used.

LUBRICATION

The best gear performances in terms of efficiency, life, temperature, will be achieved with a polyglycol lubricant such as MOBIL GLYGOYLE 30 or equivalent. The ratings shown on page 7 can be considered only if this kind of

It is recommended to use tapper roller bearings on output shaft, in order to allow an axial displacement of the wheel, during the mounting operations, to center the gear correctly. The contact pattern can be checked with Prussian blue or any similar product. A good pattern should be located slightly on the right side of the wheel tooth flanks (on both sides). It is normal to have no contact on the left side of the flanks. This gap is necessary for a good oil film forming. See sketch below.



lubricant is used.

Before use, check that the inner paint of the housing is compatible (Epoxy paints can be used).

Otherwise, use MOBIL SHC 634 or equivalent.

BACKLASH ADJUSTMENT

The accuracy of our servo gearsets **DYNASET** allows them to be set to less than 1 arcminute of backlash, without any efficiency or torque capacity losses (it is assumed than custom machined parts and mounting are correct).

If our backlash adjustment device is used, simply remove some shims (delivered) between the bearing bush and


the housing, until the desired backlash value is obtained.

For high speed applications, a backlash between 0,5 to 1 arcminute is recommended.

For very intermittent applications (rotary tables or milling heads of CNC machines for ex.), a backlash down to zero is tolerated, as soon as the no load input torque does not vary more than \pm 30 % around the average value.

16


SERVO GEARSET DYNASET



Surfaces marked ⊕ → can be referred to for checking runnout

DYNASET	35	45	55	63	75	90	110
A (H6)	32	47	52	71	82	103	136
B Maxi	55	78	92	108	124,5	157,4	191,4
С	33	38	43	46	52	57	60
D	63,5	80	85	97	126,5	144	173
Е	14	19	28	27	32	38	40
F	30,5	40	46	46,5	53,5	57,5	56
G	32	40	42	47,5	63	70	82
H Maxi	31	37,6	43,7	49,7	54,7	67,5	75,5
I Maxi	13,5	17,3	20,5	23,4	26,3	33,2	36,1
J (h6)	12	15	18	20	24	28	32
K	17	20	22	24	28	28	36
L	8	9	10	11	13	14	15
M	M15 x 1,00	M17 x 1,00	M20 x 1,00	M25 x 1,50	M 30 x 1,50	M35 x 1,50	M40 x 1,50
N (k6)	15	17	20	25	30	35	40
0	20	24	26	32	37	42	47
P Maxi	24,7	26,5	32,5	37,1	44,2	50,8	56,5
Q	24	30	30	35	42	42	47
R (k6)	20	25	25	30	35	35	40
S	3,5	4	4	4	5	6	8
Т	38	54,5	60	79	91	113	148
U	19	23,9	23,9	28,6	33	33	37,5
U1	1,3	1,3	1,3	1,6	1,6	1,6	1,85
V (h11)	20	25	25	30	35	35	40
W	5	5	5	6	6	6	6
X	35	45	55	63	75	90	110
Υ	4	6	8	10	10	10	10
Z	8	12	15	16	17	17	18

BACKLASH ADJUSTMENT DEVICE FOR DYNASET



DYNASET	35	45	55	63	75	90	110
D	42	47	52	62	72	72	80
Y Maxi	43,5	54	58	65	84	94	110
Y Mini	38,5	49	53	59	78	88	104
P Maxi	69	83	91	100	121	131,5	150
P Mini	64	78	86	94	115	125,5	144
Q	55	67,5	75	84	104	114,5	132
R	9	10,5	10	10	11	11	12
S	M6	M6	M8	M8	M10	M10	M10
Т	55	65	66	80	90	100	100
Z	58	75	75	95	95	115	115
X	16004	6005	6205	6206	6207	6207	6208

The backlash adjustment device is delivered mounted and preset.

Bearings are factory preloaded.

Backlash adjustment is operated with shims located between the housing and the bearing bush.

HOW TO ORDER

Use following codification to order your **DYNASET.**

